


Filter cartridge amaGuard HF-PP

1. Introduction

The amaGuard HF-PP, high flow filter cartridge utilises a unique pleating configuration to maximise flow rate and dirt holding capacity. The amaGuard HF-PP has been developed for a large variety of industrial processes where a high performance is required. Low pressure drop and high dirt holding capacity makes the amaGuard HF-PP an ideal choice for many applications. Flow is from inside out and the unique pleat geometry has been optimised to take advantage of this.

Typical amaGuard HF-PP applications

- Process water
- Pre-RO treatment
- Refineries - pre & final filtration
- Amines
- Oil & gas production
 - Seawater injection
 - Well injection chemicals
- Food & beverage
- Pre & final filtration of chemicals
- Desalination
- Petrochemicals
- Pulp & paper



2. Features

- All polypropylene construction
- Melt blown polypropylene filter media Inside to out flow captures all contaminants within the filter element
- Sturdy construction for use in demanding applications
- Unique pleat geometry to enable consistent flow rates with low Δp
- Large filtration area which significantly reduces the footprint of installation
- Absolute retention ratings from 1 μm to 40 μm
- High effective filtration area
- Manufactured in cleanroom 10,000

4. Product / Performance specifications

Filter medium : polypropylene
 Support medium : polypropylene
 Hardware : polypropylene
 O-Rings : EPDM, silicone, Viton®

Dimensions

Internal diameter : 70 mm
 External diameter : 152 mm
 Length : see ordering information
 Filtration area : 5.6 m²/40" cartridge

Maximum recommended differential pressure

Design : 5.1 bar at 25 °C
 Operation : 2.1 bar at 25 °C

Maximum operating temperature
 65 °C

3. Food safety

Food safety

The filter cartridges comply with the requirements of the 'Food and Drug Administration (FDA)' title 21 of the "Code of Federal Regulations" 177.1520.

Bio safety


The components of the filter cartridges (excl. O-ring) pass the USP Biological Reactivity and Chemical-Physical tests for CLASS VI plastics.

Safe for use in pharmaceutical applications.

Extractable substances

The cartridges are free of surfactants, lubricants, antistatic agents, binders and adhesives.

5. Water flow rate for 40" cartridge



x=Flow rate
 y=Clean pressure drop

Optimum recommended flow rates	
Element length	Flow rate for optimum performance / element [m ³ /h]
20"	25
40"	50
60"	70

6. Ordering code

Example

amaGuard HF-PP	1	20	U	X19	S
Cartridge type	Micron rating [μm]	Nominal length [inch]	Hardware material	Cartridge style	O-Ring material
	1	20 (527 mm)	U=polypropylene	X19	E=EPDM
	4.5	40 (1038 mm)			S=Silicone
	10	60 (1538 mm)			V=Viton®
	20				
	40				



Authorized MAHLE-Nowata Distributor & Representative

For pricing and information please call
 Commercial Filtration Supply at (855)-236-0467

Visit us Online at: www.commercialfiltrationsupply.com
 for more filtration products.