

Cost-effective filter bags for demanding applications

Eaton's ABP filter bags are suitable for a wide range of applications such as beverage filtration, fine particle removal in parts cleaning, activated carbon removal in process systems, the final filtration of vinegar, lacquers, hydraulic oils and lubricants and many more.

With efficiencies greater than 99%, each ABP filter bag model provides cost-effective filtration solutions for demanding applications. The four models ensure that users can efficiently remove particles ranging from 1 – 25 µm while delivering a long service life.

Features and benefits

- ABP polypropylene filter bags are fabricated from hydrophobic microfiber filter material, which require pre-wetting with an aqueous solution (full details about wetting and installation are provided with every box of ABP filter bags)
- Highly efficient melt-blown filter material in polypropylene with graded density profiles to maximize dirt-holding capacity and prolong service life
- No additives such as resins, binders or surface treatments
- Spunbond polypropylene cover layer virtually eliminates fiber migration

- Unique UNI-WELD process for bottom seam provides a stronger, more flexible weld
- Fully-welded construction with patented SENTINEL® seal ring provides 100% bypass-free filtration
- The pressure-activated SENTINEL seal ring provides a flexible, chemically resistant seal which adapts to any bag filter housing

Filter specifications

Material

Melt-blown polypropylene

Cover layer

Spunbond polypropylene

Seal ring

Welded polypropylene SENTINEL seal ring

Retention ratings¹

1, 5, 10, 25 µm @ > 99% efficiency

Dimensions/Parameters

Sizes

03: Ø 4 x 9" L (100 x 230 mm) 04: Ø 4 x 15" L (100 x 380 mm)

Filter area

03: 0.9 ft² (0.08 m²) 04: 1.7 ft² (0.16 m²)

Max. operating temperature

Polypropylene: 194 °F (90 °C)

Max. differential pressure 36 psi (2.5 bar)

Recommended change-out pressure for disposal²

11.6 - 21.7 psi (0.8 - 1.5 bar)

Max. flow rates³

03: 13 GPM (3 m³/h) 04: 22 GPM (5 m³/h)


FDA/EC conformity

All polypropylene materials used in manufacturing comply with the regulations of the Food and Drug Administration (FDA), title 21 of the Code of Federal Regulations Section 177, and EC Regulations 1935/2004 and EC Directive 2002/72/EC, as applicable for food and beverage contact.



ABP Filter Bag Range


Flow rates



Filter removal efficiency

Retention ratings ¹ (µm)	Particle sizes (µm) at common removal efficiencies (%)				Max. operating
	> 60%	> 90%	> 95%	> 99%	temperatures °F (°C)
1	-	1	2	4	194 (90)
5	1	2	4	5	194 (90)
10	2	5	10	30	194 (90)
25	10	30	40	-	194 (90)

Ordering information





Authorized Eaton Filtration Distributor & Representative

For pricing and information please call Commercial Filtration Supply at (855)-236-0467

Visit us Online at: <u>www.commercialfiltrationsupply.com</u> for more filtration products.

¹ Reference values based on single pass tests in ambient lab conditions with ISO test dust in water at 44 GPM (10 m³/h)/size 02.

² Dependent on the respective applications and their requirements.

³ For liquids with a dynamic viscosity of 1 mPa·s @ 68 °F (20 °C).